



PHARMACY MACHINE

Pharmaceuticals • Herbsals • Cosmetics • Food Machinery



SCAN ME



Colloid Mill

Model	JM-80L	JM-100L	JM-120L	JM-140L
Fineness (um)	2-50	2-50	2-50	2-50
Capacity (ton/h)	0.3-1	0.5-2	0.7-3	0.8-4
Motor Power (kw)	2.2	3	4	7.5
Rpm (motor)	2900	2900	2900	2900



Oscilating Granulator Machine

Model	YK-160
Capacity (kg/h)	100-300
Power (kW/V/Hz)	3/380/50



Rotary Wet Granulator

Model	ZLG-150	ZLG-250	ZLG-350
Power (Kw)	1.5	3	5.5
Capacity (kg/h)	30-100	300-400	400-600
Diameter Granule (mm)	1.2-3	1.2-3	1.2-3
Size (mm)	700x400x700	1200x700x1100	1350x800x1300




CSJ-P Crusher

Model	CSJ-P40
Capacity (kg/hour)	100-500
Size of input granules (mesh)	<300
Size of output granules (mesh)	2-20
Power (Kw)	5.5
Speed of pronicpalxis (rpm)	500
Overall Dimension (LxWxH)	780x800x1300
Weight (kg)	500




B Grinding

Model	20B	30B	40B
Production Capacity (kg/h)	60-150	100-300	160-800
Crushing Fineness (mesh)	40-120	40-120	40-120
Motor Power (kw)	4	5.5	11
Overall Dimension (mm)	600x600x1450	600x700x1450	800x900x1550
Weight (kg)	280	350	550



Grinding with Dust Collector

Model	20B	30B	40B
Capacity (kg/h)	60-150	100-300	160-800
Crushing Fineness (mesh)	60-150	60-120	60-120
Crushing Motor (kW)	4	5.5	11
Dust Collecting Motor (kW)	1.1	1.1	1.1



Double Cone Mixer

Model	W-100	W-300	W-500	W-1000
Full volume (m3)	0.1	0.3	0.5	1
Capacity (liter/batch)	40	120	200	400
Power (kW)	1.1	2.2	3	4



Fitz Mill

Model	GFSJ-8B	GFSJ-16B	GFSJ-32B
Motor (kW)	4	7.5	11
Capacity (kg/h)	10-100	50-300	100-350
Fineness (mesh)	12-120	12-120	12-120
Size (mm)	1050x600x1600	1100x860x1520	1280x950x1600



V-Type Mixer

Model	VI-100	VI-300	VI-500	VI-1000
Capacity (m ²)	0.1	0.3	0.5	1
Loading Capacity (L)	40	120	200	400
Length (mm)	1900	2010	2220	2400
Width (mm)	800	850	900	950
Rotating Speed	15	15	15	15
Motor Power(kW)	1.1/0.75	3/1.1	4/2.2	5.5/2.2




Grinding and Granulating (Cone Mill)

Model	FZB-150	FZB-300	FZB-450	FZB-700	FZ-1000
Capacity (kg/h)	15-150	30-300	45-450	70-700	100-1000
Mesh	6-80	6-80	6-80	6-80	6-80
Motor Power(kW)	1.5	1.5	2.2	3	5.5
Speed-adjusting Range (rpm)	300-3600				

Vibro Separator & Filter



Model	LS-300T	LS-450SN	LS-500-1S/2S/3S	LS-600-1S/2S/3S	LS-800-1S/2S/3S	LS-1000-1S/2S/3S	LS-1200-1S/2S/3S	LS-1500-1S/2S/3S
Power (Hp)	1/6	1/2	3/4	3/4	1	2	2.5	3



Two Dimension Mixer (Rocking Mixer)

Model	EYH-300	EYH-600	EYH-800	EYH-1000A	EYH-1500A
Barrel Volume (L)	300	600	800	1000	1500
Loading Capacity (L)	180	360	480	600	900
Max Loading Weight (kg)	90	180	240	300	450
Swing & Rotation (r/min)	18/11	16/19	10/6	8/6	9/5
Total Motor (kW)	1.3	2.2	3	3	4.4

Kneading Mixer

Model	SCH-200	SCH-400	SCH-600/800
Working Volume (Liters)	200	400	600
Motor Power (kW)	5.5/1.1	11/2.2	15/3


Super Mixer

Model	LM-10	LM-50	LM-100	LM-200	LM-300	LM-400
Total Volume (liters min)	10	50	100	200	300	400
Working Capacity (liters)	2-6	12-36	25-70	50-150	60-220	100-280
Rotational Speed of Stirring Paddle (rpm)	50-500	50-500	30-360	30-260	20-200	20-200
Power Motor of Stirring Paddle (Kw)	2.2	5.5	7.5	15	22	22
Rotational Speed of Cutter (rpm)	50-3000					
Power Motor of Cutter (Kw)	0.75	1.5	3	4	7.5	7.5



Fluid Bed Dryer

Model	FL-30	FL-60	FL-120	FL-200	FL-300	FL-500
Hopper Volume (L)	100	220	420	670	1020	1560
Material Feed/Batch (kg)	30	60	120	200	300	500
Fan Power (kW)	7.5	11	22	30	36	45



Stainless Steel Drying Oven

Model	RXH-7C	RXH-14C	RXH-27C
Capacity (kg/batch)	60	120	240
Electric Heating/Steam Heating (kW/V/Hz)	9/380/50	15/380/50	30/380/50



Series GZP-500 High Speed Rotary Tablet Press

Model	GZP-35	GZP-43	GZP-51	GZP-55	GZP-57
Number Of Station (set)	35	43	51	55	57
Max Main Pressure (KN)	100	100	100	100	100
Max Pre-pressure (KN)	20	20	20	20	20
Max Tablet Diameter :					
Round (Irregular tablet) (mm)	25(25)	18(19)	13(16)	13(16)	11(13)
Max production Capacity (pcs/h)	252000	309600	367200	396000	410400
Motor Power (kw)	11	7.5	7.5	7.5	7.5
Overall Size (mm)	1370x1170x1800				

Series ZP1100(A) Rotary Tablet Press

Model	ZP-1124(A)	ZP-1129(A)	ZP-1134(A)	ZP-1136(A)	ZP-1139(A)
Number of Station (set)	24	29	34	36	39
Max. Pressure (kN)	80	80	80	80	80
Max. Pre Pressure (kN)	20	20	20	20	20
Max. Dia of Tablet (mm)	25(25)	18(19)	13(16)	13(16)	11(13)
Max. Capacity (pcs/h)	93600	113100	132600	140400	152100
Motor (kW)	4	4	4	4	4

ZP1100A model is equipped with force feeder

Rotary Tablet Press Machine



Model	ZP27	ZP29	ZP31
Number of Stations (set)	27	29	31
Max Main Pressure (KN)	100		
Max Tablet Diameter (mm)	25		
Max Filling Depth (mm)	15		
Max Tablet Thickness (mm)	6		
Max Turret Speed (r/min)	30		
Max Production Capacity (pcs/h)	97200	104400	111600
Motor Power (Kw)	5.5		
Dimension (mm)	1140x1000x1650		

Model	ZP-35B
Station (set)	35
Max. Pressure (kN)	80
Max. Pre Pressure (kN)	20
Max. Dia of Tablet (mm)	13(length 16mm)
Max. Capacity (pcs/h)	150000
Motor (kW/V/Hz)	4/380/50

Model	ZP5	ZP7	ZP9
Number of Station (set)	5	7	9
Max Tablet Pressure (KN)	40		
Max Tablet Diameter (mm)	Round Tablet Irregular Tablet		
	13 16		
Max. Tablet Thickness (mm)	6		
Max. Production Capacity (pcs/h)	7500	10500	12000
Motor Power (Kw)	1.5		
Dimension (mm)	660x480x1050		




Rotary Tablet Press Machine

Model	ZP-8	ZP-10	ZP-14	ZP-17	ZP-21	ZP-23
Station (set)	8	10	14	17	21	23
Pressure (kN)	60	60	60	60	60	60
Pre-pressure (kN)	10	10	10	10	10	10
Max. Dia Tablet (mm)	25(25)	25(25)	18(19)	18(19)	13(16)	11(13)
Max Production Capacity (pcs/h)	14400	18000	25200	30600	37800	41400
Motor Power (kW)	1.5	1.5	1.5	1.5	1.5	1.5



ZP130 Series Rotary Tablet Press

Model	ZP5A/B	ZP7A/B	ZP9A/B
Number of Stations	5	7	9
Max. Main Pressure (KN)	40/60	40/60	40/60
Max. Tablet Diameter (mm)	13/20	13/20	13/20
Max. Filling Depth (mm)	15	15	15
Max. Tablet Thickness (mm)	6	6	6
Max. Turret Speed (r/min)	25	25	25
Max. Production Capacity (pcs/h)	7500	10500	12000
Motor Power (kw)	1.5/2.2	1.5/2.2	1.5/2.2
Overall Size (mm)	660x480x1050	660x480x1050	660x480x1050
Weight (kg)	350	350	350



Automatic Auger Powder Filler

Model	DCS-2A
Output (Boto/min)	20-60
Fillif Range (gr)	10-500
Power (kW/V/Hz)	1/380/50



Automatic Screw Blanking Powder Filling Machine

Model	FLG-20A	FLG-500A
Voltage (Volt/Hz)	AC 220/50 110/60	
Power (Kw)	1	1
Packing Capacity (ml)	1-20	50-500
Capacity (pcs/min)	20-50	20-40
Dimension (mm)	850x500x1850	
Weight (kg)	150	



Vacuum Transfer Powder

Model	QVC-1	QVC-2	QVC-3	QVC-4	QVC-5
Capacity (kg/h)	350	700	1500	3000	6000
Dimension (mm)	140x560	213x720	290x850	420x1100	420x1350



Soft Plastic Tube Filling And Sealing Machine

Model	RGNF-30B
Filling Volume (ml)	5-250(tube)
Filling Accuracy	≤±1%
Capacity (tubes/h)	1800-2400(Adjustable)
Tube Diameter (mm)	φ10- 50
Tube Length (mm)	210(Max. Length)
Hopper Volume (L)	40
Power (V)	380/220(Optional)
Compressed Air (Mpa)	0.5-0.7
Hot Air (kw)	3.0



Semi-auto Capsule Filling Machine

Model	CGN208-D
The Time of Replacing Debugging Mold (mins)	5-8(for beginners)
Production Rate (ten thousand/hour)	1-2.5 (depending on capsules No.)
Filling Material	Without a sticky and wet powder,small granules
Power (kw)	4.0
Air Pressure	0.03m ³ /min 0.6Mpa
Vacuum Pump Capacity	40m ³ /h
Dimension (mm)	1140x700x1630
Weight (kg)	350




Auto Capsule Filling Machine

Model	NJP-800	NJP-1000	NJP-1200
Filling Dosage	Powder, Pellets, Tablet	Powder, Pellets, Tablet	Powder, Pellets, Tablet
Max.Output (capsules/h)	48000	60000	72000




Film & Sugar Coating

Model	BG-40D	BG-80D	BG-150D
Capacity (kg/run)	40	80	150



Blister Packing

Model	DPP-140C(S)	DPP-250C(S)
Wrapping Material (mm)	140	250
Power (kw/V/Hz)	6/380/50	6/380/50




Automatic Strip Packaging Machine Chuan Yung - Taiwan

Model	CY-AP-M6	CY-AP-M10
Capacity (pcs/min)	1000-1800(10 line)	1200-2400(12 line)
Max Package Width (mm)	300	350
Electrical (kW/Volt/Hz)	0.75/220/50	0.75/220/50
Heater Power (kW)	3	3
Compressed Air (Mpa)	0.45	0.45




Semi Automatic Liquid/ Pasta Filling Machine

Model	MN-02
Filling range (cc)	5-200 and up
Applicable viscosity (cps)	200-500
Power consumption (W)	500
Dimension (mm)	550x550x350
Weight (kg)	33



DYF One Head Liquid Filling Machine

Model	DYF		
Power Supply (V/Hz)	220/110 / 50/60		
Air Pressure (Mpa)	0.4-0.6		
Filling Speed (bottles/min)	5-20		
Filling Range (ml)	25-60	50-125	100-250
	200-500	400-100	900-2500
	2200-5000		



DGF One Head Ointment Filling

Model	DGF		
Power Supply (V/Hz)	220/110 / 50/60		
Air Pressure (Mpa)	0.4-0.6		
Filling Speed (bottles/min)	5-20		
Filling Range (ml)	25-60	50-125	100-250
	200-500	400-100	900-2500
	2200-5000		



Capsule Polisher With Sorter

Model	JFP-110A
Working Capacity (pcs/hour)	150000
Power Supply	220V/50Hz/2A/180W
Negative Pressure	2.7m³/min - 0.014Mpa
Compressed Air	0.25m³/min - 0.3Mpa
Overall Dimension (mm)	800x550x1000




Polishing Capsule

Model	YPJ-II
Maximum Output (capsules/min)	Max. 7.000
Motor Power (W/V)	185/220
Dimension (mm)	1310x405x1200




Uphill Tablet Deduster

Model	SZS-230
Max output capacity (t/h)	800.000 (Ø6mm Tablet)
Dedust route (m)	6
Max lift height (mm)	1220
Max tablet Dia. (mm)	Ø25
Power supply (Ph/V/Hz)	1 / 220/110 / 50-60
Outer dimension (mm)	550x550x(H:1350-1500)
Weight (kg)	70
Compressed air (Mpa)	0.1m³/min 0.05
Vacuum (Mpa)	2.7m³/min-001




Tablet Deduster

Model	CFQ-1
Output (tablet/h)	550.000(Ø 6 round)
Power Supply (V/Hz/W)	220/50/50
Overall size (mm)	410x410x880




Automatic Filling Liquid & Capping Machine

Model	YGX
Output (botol/min)	40-60
Power (kw/V/Hz)	1.5/380/50



Automatic Labelling Glue Machine

Model	TB-80(Glue)
Labelling Speed (bottles/min)	60-80
Label Width (mm)	40-110
Label Long (mm)	50-130
Dimension (mm)	2100x950x1000
Power (V/kw)	220/380 / 1.5



Batch Counter

Model	KW-102
Output (Capsules/min)	1000-2000
Power Supply (V/Hz/Ph)	Ac 110/220 / 50/60 / 1
Power Consumption (kw)	0.2



Semi Automatic Sticker Labeling Machine

Model	KP-T-200
Labelling Accuracy (mm)	±1
Labelling Speed (pcs/min)	15-35
Applicable Diameter (mm)	ø15-120
Applicable Width (Backing Paper) (mm)	10-160
Applicable Length (mm)	15-330
Dimension (mm)	950x420x500
Power (W)	220
Voltage (V/Hz)	220/50
Weight (Kg)	35



Automatic Labelling Sticker Machine

Model	APP-500(stiker)
Labelling Speed (bottles/min)	35
Label Width (mm)	10-120
Label Long (mm)	20-300
Dimension (mm)	2000x1300x1400
Power (V/kw)	220/0.96



Dissolution Tester

Model	RC-8DS
Size (mm)	680x540x480



Disintegration Tester

Model	BJ-2
Size (mm)	400x300x420



Tablet Hardness Tester with Printer

Model	YD-2
Test Range	2-199.9N
Size (mm)	500x300x160



Front and Back Side Stick Labeller

Model	LMD-250X
Labelling Speed (bottles/min)	50-100
Label Width (mm)	20-120
Label Long (mm)	20-300
Dimension (mm)	2500x1200x1700
Power (V/W)	220/250



Single Punch Tablet Press M/C

Model	TDP-1.5T
Max. dia. of tablet (mm)	12
Power	550W/220V, 50Hz



Tablet Friability Tester

Model	CS-2
Cylinder Number	2
Size (mm)	360x300x340



Head Office :

Jakarta

Jl. Pangeran Jayakarta, Komp 117, Blok A No. 8-10
Jakarta Pusat 10730

Phone : (021) 6599 657, 6249 282

Fax : (021) 6497 850, 6008 474

Mail : sh@sinarhimalaya.com

Branch Office :

Surabaya

Jl. Kedungdoro No. 36-46 Blok 6-7
Surabaya 60251

Phone : (031) 5322 160, 5342 735, 5344 035

Fax : (031) 5316 113

Mail : shsby@sinarhimalaya.com

Semarang

Jl. Majapahit No. 119A
Semarang 50161

Phone : (024) 6711 822, 6711 829, 7692 8639

Fax : (024) 7674 1786

Mail : shsmr@sinarhimalaya.com

Medan

Jl. T. Amir Hamzah No. 50 C-D
Medan 20117

Phone : (061) 8008 9000, 8008 9054

Fax : (061) 8008 9104

Mail : shmdn@sinarhimalaya.com

Follow us on :



www.sinarhimalaya.com



@sinar_himalaya



Sinar Himalaya



Sinar Himalaya